



0 Reviews



0 Reviews

 Need Help?

SHOP PRODUCTS

All ▾

Search by keyword, connector, or sku



LIVE CHAT & HELP ▾

[Browse All Products](#)[Networking](#)[Racks, Cabinets, Panels & Enclosures](#)[Vertical Wall Mount Cabinets](#)

8RU Vertical Wall-Mount Cabinet with Split Door - 36in Height

Provide a convenient and easy to use solution for edge, lot, PoE and network requirements with limited space



0 Reviews

Product # : VWMSD-8RU-36-B

 Roll over image to zoom inIn Stock, only 7 left 

Add



Need it shipped today?

Select FedEx Priority or 2nd Day shipping.

 print  share  chat

Product Info

 Customer Reviews Questions & Answers Distributors

Description

Features

Specs

Support

Product Description

The Legrand VWM Series wall mount cabinets provide a ultra low profile and easy to use solution, perfect for secure networks, small data closets, retail, educational, edge computing, and all areas where floor space is limited.

Convenience

The split door design allows for user access at the top, while protecting critical equipment behind the front door. Mounting small routers, hubs, and computers that are non-rack mountable is also simplified with the optional patented Lever Lock equipment panels. When customized with many of the optional accessories, the vertical wall-mount cabinets can accommodate many complete computing combinations.

Durability

The VWM cabinets are made of rugged welded steel and have a UL 2416 certified load rating of 150 lbs. The small form factor cabinets are PCI compliant, have a 31" equipment mounting depth and feature solid locking doors that provides security for the installed equipment.

Product Features

- Certified load rating of 150 lbs per UL2416
- PCI Compliant
- Full swing handle
- Reversible hinged front locking door
- Split door design
- Patented Lever Lock System
- Versatile rail mounting locations
- Cable and fan knockouts

**WARNING:** Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Specifications

Color :

Black

Warranty :	5 years
Vendor :	Legrand
Weight :	94.000 LB

Physical Specifications:

- Door Type: Split Door
- Rack Units: 8RU
- Equipment Mounting Depth: 31 in
- UL 2416 Certified Load Rating: 150 lbs
- Unit Dimensions H x W x D: 36 x 26 x 18 in
- Shipping Dimensions H x W x D: 39.5 x 29 x 21.5 in
- Unit Weight: 84 lbs
- Shipping Weight: 94 lbs
- Certifications/Compliances: TAA Compliant, UL2416 Certified, PCI Compliant, EIA-310-E Compliant, RoHS Complaint, Product Environmental Profile (PEP) Compliant

Product Support

Downloads

- Download the [Data Sheet](#)
- Download the [Specification Sheet](#)
- Download the [Drawing](#)
- Download the [Spec Comparison Sheet](#)
- Download the [Instruction Sheet](#)

Info

About Us

Order History

Where To Buy

More ▾

Service

Contact Us

OEM Solutions

Tech Support

More ▾

Resources

Connector Guides

ConnectXpress

Drivers & Manuals

More ▾

Have A Question?

Get help with [Chat](#)

Call C2G **800.506.9607**

f

t

y

b