

Twist-Lock® Devices
20A, 250V AC, 2 Pole, 2 Wire Non-Grounding
Insulgrip® Connector

Features

- Insulated nylon construction to keep non-current carrying parts from becoming energized
- Tough ribbed nylon housing for secure gripping
- Two-part cord grip tightens with two screws for maximum retention force.

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Black and white nylon	.230"-.720" (5.6-18.3)	783585177007	HBL7101C

Listings


Listed to UL Standard 498
Fed Spec W-C-596

Specifications

Body	Nylon
Terminal Retainer	Clear polycarbonate
Contacts	Bronze
Terminal Screw	Brass
Terminal Clamp	Cold rolled steel – nickel plated
Assembly Screws	Steel - zinc plated

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Terminal Accommodation	#18 AWG - #10 AWG stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Accessories

Plug	HBL7102C
Weatherproof Boot	HBL6024

Resources

Customer Use Drawing
eCatalog

