




|                  |                            |
|------------------|----------------------------|
| Rotating angle   | 90°                        |
| Contact function | 2 NC + 2 NO                |
| Contact system   | Bridge-snap-action contact |
| Contact material | Silver                     |
| Solderability    | Yes                        |
| Locking          | 45                         |

**> electrical data**

|                     |        |
|---------------------|--------|
| Rated voltage, min. | 12 V   |
| Rated voltage, max. | 230 V  |
| Rated current, min. | 0.05 A |
| Rated current, max. | 4 A    |

## drawings

### Dimensioned drawing



### Mounting hole drawing

