





GSD

KC-59-482

REVISIONS		
ISSUE	CHANGES	
3	CN 23087 D	MD 23 FEB 82
4	CN 37034 D	JUS 06/28/96

- NOTES:
1. FOR USE WITH BELDEN 9259 CABLE
 2. FOR CABLE TRIMMING USE KTU-57 & KTD-26.
 3. FOR CRIMPING USE DIE SIZE 02.
 4. FOR CABLING INSTRUCTIONS SEE CP-401.
 5. MATERIAL:

- INSULATOR- TEFLON, L-P-403
 GASKET- SILICONE RUBBER, ZZ-R-765
 K-GRIP SLEEVE- HARD DRAWN COMMERCIAL BRONZE, ALLOY 220
 OUTER CONTACT- BERYLLIUM COPPER, QQ-C-530
 ALL OTHER METAL PARTS- BRASS, QQ-B-626
6. FINISHES:
 CENTER CONTACT } SILVER PLT. PER QQ-S-365
 SPRING WASHER }
 ALL OTHER METAL PARTS- KINGS TARNISH RESISTANT FINISH (TR-5)
7. ELECTRICAL CHARACTERISTICS:
 NOMINAL IMPEDANCE- 50 OHMS
 FREQUENCY RANGE- DC TO 4 GHz
 WORKING VOLTAGE- 500 RMS

GSD

SCALE 4:1	
APPROX SURFACE AREA	
USED ON	
REF:	
BNC PLUG	
DRAWN JCA	DATE 06/28/96
DESIGN MJB	DATE 06/28/96
APPR.	DATE

KINGS
 ELECTRONICS CO., INC.
 TUCKAHOGE, NEW YORK 10707

KC-59-482