

432BAU6W

Panel mounted inlet

2CMA166664R1000



Inlet Panel Mounting, unified flange, angled, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA166664R1000
Function	Inlet, panel mounting, unified flange, angled
EAN	73926966666
Catalog Description	Inlet, panel mounting, 6h, 32A, IP67, unified flange, angled, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421562
E-Number Norway	1542663
E-Number Sweden	E2417399
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	101 millimetre
Product Net Height	101 millimetre
Product Net Length	107 millimetre
Product Net Depth	107 millimetre
Product Net Weight	0.32 kilogram

TECHNICAL

Product Main Type	TBAU
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...10 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

PACKAGING

Package Width	112 millimetre
Package Height	139 millimetre
Package Gross Weight	0.37 kilogram
Package Length	112 millimetre
Package Units	box 1 piece