




FCIconnect.com


Copyright FCI



PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	GLASS FILLED THERMOPLASTIC RATED (UL94V-0)	1	COLOR:BRACK
2	CONTACT	BRASS	n	PLATING CONTACT AREA:GOLD OVER NICKL TERMINAL AREA:TIN (LEAD FREE)
3	MOUNTING PLATE	PHOSPOR BRONZE	2	PLATING:TIN (LEAD FREE)

RECOMMENDED PC BOARD LAYOUT
THICKNESS : 1.6
HOLE PATTERN (COMPONENT SIDE)

n:NO. OF CONTACTS
(10 TO 30 , ONLY EVEN POS.)



NOTE
1.This product meets European Union
Directives and other country regulations
as described in GS-22-008.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family 590F		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title FLOATING BOARD TO BOARD RECEPTACLE CONNECTOR (GOLD PLATING AND LEAD FREE) (Cat. No. BTFW_R-3RDA7MLF)		
A	J07-0021	M.K	Jan.25,07	angles	linear	±0.3	scale		
				dr	K.Higuchi	Jan.25,07	dwg no sheet 1 of 1 size		
				enr	M.Koga	Jan.25,07	JSA 97219 A4		
				chr	K.Higuchi	Jan.25,07	type Product Customer Drawing		
				appd	M.Koga	Jan.25,07			
sheet index	revision sheet								Rev A