

Part Number : [1110150200](#)

Product Description : HSAutoLink Cable Assembly, USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 1.00m Length, Polarization A

Series Number : 111015

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

[1110150200_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-68800-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	111015
Description	HSAutoLink Cable Assembly, USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 1.00m Length, Polarization A
Application	Automotive
Assembly Configuration	Dual Ended Connectors
Comments	USCAR-30 Compliant
Connector to Connector	USB Type A-to-Mini-B
Product Name	HSAutoLink USCAR/USB
UPC	883906510084

Physical

Cable Length	1.0m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	59.314/g
Number of Rows	1
Single Ended	No
Wire/Cable Type	Round

Mates With / Use With

Mates with Part(s)

Description	Part Number
HSAutoLink Right-Angle Headers	<u>49616</u>

This document was generated on Oct 06, 2026