



Search by Model No. or I

Sign
in

Resister

Japanese | **English**

Product Category Environment About SATO PARTS Contact us My list

SATO PARTS CO.,LTD. > Product Category > Binding.post / Tip Plug & Jack

Precautions for use General notes

TJ-10-A made in JAPAN



2013-05-13 Notice of partial product changes. See other change notifications



Order model number

Order model number TJ-10-A-[Body color]
Order example TJ-10-A-R (An example of an order with a red color.)

Basic information Dimension Soldering heat resistance conditions Conformity product / Mate product Download
Add to My List Sample request (Only >



dy color

Sign
in

Resister

Japanese

English

Product Category

Environment

About SATO PARTS

Contact us

My list

R

B

Basic information

Rating	30V-5A
Insulation resistance	DC500V、100MΩ Min
Withstand voltage	AC1000V (1minute)
How to mount	With nut
Nut torque	0.3N・m Max
Main insulator	Nylon6
Body color	R (Red)、B (Black)
Mate	TJ-2-P、TJ-100-KC attached to TJ-100.

List of partial product change notifications

2013-05-13 Notice of partial product changes.

Add to My List





Sign
in

Resister

Japanese | **English**

Product Category

Environment

About SATO PARTS

Contact us

My list

Home

Product search

Product Category

About SATO PARTS

News classification

Contact us

Video channel

Download brochure

Environmental
initiatives

Privacy policy

Cookie policy

Download terms

Terms of Use

Privacy policy | Site map

COPYRIGHT © SATO PARTS CO.,LTD. ALL RIGHTS RESERVED.

Add to My List >

>