



Color: ■ gray Similar to illustration

Electrical data	
Rated current	16 A

Physical data	
Width	12 mm / 0.472 inches
Height	10 mm / 0.394 inches
Depth	5 mm / 0.197 inches

Material data	
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.009 MJ
Weight	0.9 g

Commercial data	
Product Group	9 (Std Chassis Mt Blocks)
PU (SPU)	500 (25) pcs
Packaging type	Box
Country of origin	PL
GTIN	4045454342463
Customs tariff number	85366990990



Product Classification	
UNSPSC	39121421
eCl@ss 10.0	27-14-11-40
eCl@ss 9.0	27-14-11-40
ETIM 9.0	EC000489
ETIM 10.0	EC000489
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Environmental requirements	
Processing temperature (min.)	-35 °C
Processing temperature (max.)	85 °C
Processing temperature	-35 ... +85 °C
Continuous operating temperature from	-60 °C
Continuous operating temperature up to	105 °C
Continuous operating temperature	-60 ... +105 °C

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 262-402

↓

Documentation			
Bid Text			
262-402	19.02.2019	xml 2.62 KB	↓
262-402	17.08.2017	doc 23.50 KB	↓

CAD/CAE-Data

CAD data

2D/3D Models 262-402

↓

CAE data

EPLAN Data Portal 262-402

↓

WSCAD Universe 262-402

↓

ZUKEN Portal 262-402

↓



1 Compatible Products
1.1 Optional Accessories
1.1.1 Tool
1.1.1.1 Operating tool



Item No.: 209-132
Operating tool; for connecting comb-style jumper bar; made of insulating material; 2-way; natural