


ALL TOLERANCES = ± 0.3
UNLESS OTHERWISE INDICATED

DESIGNED TO ACCOMMODATE STANDARD:
D-SUB - Shell Size 2

BACKSHELL KIT INCLUDES:

- 2 - BACKSHELL HALVES
- 2 - MATING SCREWS (#4-40, RECOMMENDED TORQUE 60 in-oz)
- 2 - SADDLE WASHERS
- 2 - HOUSING SCREWS (#4-40, RECOMMENDED TORQUE 5.2 in-lbs)
- 2 - HOUSING NUTS (#4-40, RECOMMENDED TORQUE 5.2 in-lbs)
- 1 - GROMMET TREE - VARIOUS SIZES (NON-CONDUCTIVE GROMMETS)

MATERIAL: DIE-CAST ZINC ALLOY
PLATING: NICKEL (5u" MIN PLATING THICKNESS)
OPERATING TEMPERATURE: -45°C TO +120°C



979-015-030R121

SERIES _____
POSITIONS _____
015 _____
MATERIAL _____
030 = ZINC _____
RoHS COMPLIANT _____
R = HIGH TEMP. PROCESS _____
PLATING _____
12 = NICKEL _____
PUT-UPS _____
1 = KIT _____

RoHS COMPLIANT

DRAWN:
C. SMITH
DATE:
4/20/2010

UNITS = mm

DO NOT SCALE FROM DRAWING





THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.


NorComp

SCALE: NTS SHEET 1 OF 2 REV 8

DWG NO. 979-015-030R121



ALL HARDWARE:
MATERIAL = STEEL
PLATING = NICKEL



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
4/20/2010

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET 2 OF 2

REV 8

DWG NO.

979-015-030R121