



Common Mode Choke

TCK-073


Order Code	TCK-073
Inductance (each winding)	305 µH ±35% (at 100 kHz / 100 mV)
Impedance (DCR)	20 mΩ max.
Rated Current	11.3 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-073



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	16.0 max.
B	16.0 max.
C	15.0 max.
D	4.0 ±0.3
E	10.0 ±0.3
F	7.4 ±0.3
G	ø 0.8

All specifications valid at +25°C, unless otherwise stated.