

316RU6

Panel mounted socket

2CMA193178R1000



Panel mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, unified flange, straight, 3-poles+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA193178R1000
Function	Panel mounted socket
EAN	7392696931786
Catalog Description	Socket-outlet, panel mounting, 6h, 16A, IP44, unified flange, straight, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421238
E-Number Norway	2416626
E-Number Sweden	E2416626
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	75 millimetre
Product Net Height	87 millimetre
Product Net Length	88 millimetre
Product Net Depth	88 millimetre
Product Net Weight	0.21 kilogram

TECHNICAL

Product Main Type	ERU
Color	Red
Number of Poles	4
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	380 ... 415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	2.1 kilogram
Package Length	158 millimetre
Package Units	box 10 piece