


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 42263	05/18	SEE PDM
A	DCN 51153	10/21	



MATERIAL:

CONNECTORS: SMA MALE (2926-6015), SMPM FEMALE (3221-40006)

CABLE: T-FLEX 405

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS
FREQ. RANGE: DC TO 18 GHz
VSWR: 1.30:1 MAX, DC TO 18 GHz
INSERT. LOSS: SEE TABLE

TABLE 1		
SV P/N	OAL	MAX INSER. LOSS
7029-2561	6.000	0.95 dB
7029-2562	12.000	1.49 dB
7029-2563	24.000	2.55 dB

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$
-----------	-----------	--