

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



CD-10BFFA-QL8SP0

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL1977

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

 Search



X-Lok, Middle Siz...
AB-CD10ML-CDFL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CD10ML-CDFL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CD10ML-CDFL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CD10ML-CDFL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CD10ML-CDFL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CD10ML-CDFL...
-20°C ~ +80°C

- 0 +

☐

 Add to Cart

 Inquiry

Specifications	Download / CAD
Nominal Current 5A	Connector Type Field Installable
Shielded Plastic, Non-shielded	No. of Contacts 10
Connector Gender Female	Backshell Straight
Mating Style Push Lock	IP Rating IP68
Assembly Style Crimp	
 More Options	

People Also Bought

