

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

FLOS & FLOS+ >

Y series C size

Accessory

B Series A Size

B Series B Size

B Series C Size

B Series D Size

K Series B Size

K Series C Size

K Series D Size

Y Series B Size

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >

ALTW Emporium >



SLKD-26FGMS-GCP-227

Operating Temperature: -40°C ~ +125°C

Transmission Speed: N/A

Shielded: Metal, Shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

 Search



FLOS & FLOS+...
CAP-WLKM0CE4
-40°C ~ +125°C

- 0 +



FLOS+, K Series D..
SLKD-26EGFS-...
-40°C ~ +125°C

- 0 +



 Add to Cart

 Inquiry

Specifications

Download / CAD

Nominal Current

2A

Connector Type

Field Installable

Shielded

Metal, Shielded

No. of Contacts

26

Connector Gender

Male

Backshell

Straight

Mating Style

Push Pull

IP Rating

IP68

Assembly Style

Solder

 More Options

People Also Bought



SLKD-26FGMS-GCP-...



M12A-10PFFS-...



AB-CB05FL-CBBL-...



BB-028FFM-LR6A10



CBD-06RFMC-...