

Cover

ML-40-3C

Name plate

ML-40-3K

Mounter

ML-40-3I1

Mounting screw

ML-40-3J

Terminal block angled metal holder

ML-40-3L1

Soldering metal

ML-40-3G

Short circuit metal

ML-1000-3H1

Short circuit metal

ML-1000-3H2

Short circuit metal

ML-1000-3H3



Terminal block banana plug
TJ-3-A



Banana plug adapter
TJ-3-B



Enlarge : Click picture, drawing.

| [Back](#) | [List](#) | [Next](#) |

To be Followed by part number.

Classification	Item	Insulation materials	Optional accessories
Cover	ML-40-3C	P.V.C (UL94V-0)	ML-40 (S1AX, S1BX, S1EX, S2AX, S3EX) ML-41 (S1AX, S1BX, S2AX)
Name plate	ML-40-3K		
Mounter	ML-40-3I1✕		
Mounting screw	ML-40-3J✕		
Terminal block angled metal holder	ML-40-3L1✕		
Soldering metal	ML-40-3G1	High impact styrol	ML-40
Short circuit metal	ML-1000-3H1		ML-40, ML-41
	ML-1000-3H2		
	ML-1000-3H3		
Terminal block banana plug	TJ-3-A		TJ-3-B
Banana plug adapter :	TJ-3-B✕		ML-40, ML-41

Important notice

ML-40-3I1/3J/3L1 Use as couple. Must order always as couple

Terminal block which mount this device will not satisfy their own current rating

How To Order

Name plate

ML - 40 - 3C-  

Series	Number of poles
ML - 40 - 3C-	1 up to 20

Name plate

ML - 40 - 3K-  

Series	Number of poles
ML - 40 - 3K -	1 up to 20

Mounter


ML - 40 - 3I1

Mounting screw


ML - 40 - 3J

Mounter


ML - 40 - 3L1

Soldering metal


ML - 40 - 3G1

Short circuit metal


ML - 1000 - 3H1


ML - 1000 - 3H2


ML - 1000 - 3H3

Terminal block banana plug

TJ - 3 - A- 


Series	Color
T J - 3 A	R(Red),B(Black)

Banana plug adapter


TJ-3-B-

Series	Size
TJ-3-B	M3, M3.5, M4, M4.5


ML-40-3C




ML-40-3K



ML-40-311




ML-40-3J




ML-40-3L1


ML-40-3G1




ML-1000-3H1



ML-1000-3H2



ML-1000-3H3



TJ-3-A

TJ-3-B

