



Discontinued Product (30.06.2023)

M2011LL4G01

Toggle switches



Catalog PDF

Support Documentation

- > [Switch User Manual](#)
- > [Product Safety Precautions](#)
- > [Materials & Conversions](#)
- > [Electrical Ratings](#)
- > [Lamps & LEDs](#)
- > [Processing Data](#)
- > [Standards & Approvals](#)
- > [Terms & Acronyms](#)
- > [Product Overview](#)

General Specifications

Part No.	M2011LL4G01
Description	Not recommended for new designs. Order due date : 2023/06/30 New Part Num.: MN11LL4G01 New PN Available to Order : 2023/7/3
Name	TOGGLE SWITCHES
Series	M
Poles	SPST
Circuits	On-Off
Current Rating	0.4VA (AC/DC)
Rating	0.4
Illumination	Non-Illuminated
Mounting Type	Panel Mount
Contact Finish	Gold Plating
Rating (AC)	28V
Rating (DC)	28V
Actuator Type	5.1mm Dia. Locking Lever
Panel Cutout Dimensions	6.5Dia.
Termination Style	Solder Lug
Standards & Approvals	UL

Accessories

- > [Cap for Locking Lever\(Code L\)/Black:AT427A](#)
- > [Cap for Locking Lever\(Code L\)/Red:AT427C](#)
- > [Cap for Locking Lever\(Code L\)/Blue:AT427G](#)
- > [Knurled Face Nut/Metric:AT501M](#)