



426P13 10/100 BASE-T CIRCUIT²₃








C1 = 1000pF, 2KV, CAPACITOR
R1 - R4 = 75 ohms, RESISTOR

SINGLE COLOR LED



BI-COLOR LED



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY REN 18AUG2006	 trp a bel group		DONGGUAN CHINA					
		CHK KEITH ZHU 18AUG2006								
DIMENSIONS: mm		APVD TEDDY XIONG 18AUG2006	DESC 1X1, MAGJACK, VERTICAL 426PI3, 10/100 CIRCUIT, W/ LEDS							
		MODEL NAME MAGJACK SINGLE NON-POE								
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.25 3 PLC ±0.25 4 PLC ±.1 ANGLES ±.1				SIZE A2	CAGE CODE C-1840419	DRAWING NO 1840419	RESTRICTED TO -			
PRODUCT SPEC 108-2100		APPLICATION SPEC -		CUSTOMER DRAWING			SCALE 4 : 1	SHEET 2	OF 2	REV G