

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [X-Lok](#) / [Mini Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[X-Lok](#) >

- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size

[M Series](#) >[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 2000](#) >[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[D-Sub](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

AU-06PMMP-QC8001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL2238, UL50e

You must login first for view the price


Quantity

- 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Accessory, 2A, 0...
AB-AU-666600-...
-20°C ~ +85°C

X-Lok, Mini Size, Plasti...
AB-AU06FL-AUFL-...
-20°C ~ +80°C

X-Lok, Mini Size, Plasti...
AB-AU06FL-AUFL-...
-20°C ~ +80°C

X-Lok, Mini Size, Plasti...
AB-AU06FL-AUFL-...
-20°C ~ +80°C

Add to Cart

Inquiry

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Specifications

Download / CAD

Nominal Current
2A

Connector Type
Receptacle

Shielded
Plastic, Non-shielded

No. of Contacts
06

Connector Gender
Male

Backshell
Circular

Mating Style
Push Lock

IP Rating
IPX8

Assembly Style
PCB 180°

More Options

People Also Bought

