


## Product Line

- [DeepTronica](#) >
- [Single Pair Ethernet](#) >
- [ZConnect](#) >
- [Ceres](#) >
- [X-Lok](#) >
- [M Series](#) >
- Accessory**
- [M5](#)
- [Guided M8](#)
- [M8](#)
- [M10.5](#)
- [M12 \(A\)](#)
- [M12 \(B\)](#)
- [M12 \(D\)](#)
- [M12 \(I\)](#)
- [M12 \(K\)](#)
- [M12 \(L\)](#)
- [M12 \(S\)](#)
- [M12 \(T\)](#)
- [M12 \(X\)](#)
- M23**
- [FLOS & FLOS+](#) >
- [Power](#) >
- [RBL](#) >
- [HS-Lok](#) >
- [NMEA 2000](#) >
- [Heavy Duty Shielded](#) >
- [RJ](#) >
- [USB](#) >
- [SSL](#) >
- [HDMI](#) >
- [DVI](#) >
- [Fiber Optic](#) >
- [RF](#) >
- [Cable Joiner](#) >
- [Cable Gland](#) >
- [Pressure Relief Vent](#) >
- [LED Light Guide](#) >
- [D-Sub](#) >



### CAP-WBDMSPB2

Operating Temperature: -40°C ~ +105°C  
Transmission Speed: N/A  
Shielded: Metal, Non-shielded  
Jacket Material: N/A  
Certificate: N/A

You must login first for view the price

Quantity  Check Stock

Add to Cart Inquiry Heart icon

Can't find? [Customize your part](#)

### Mating Pair & Accessories

Connector Type Search

☐

☐

☐

☐

☐

☐

Add to Cart

Inquiry

| Specifications                         | Download / CAD                          |
|----------------------------------------|-----------------------------------------|
| Nominal Current<br><b>N/A</b>          | Connector Type<br><b>Waterproof Cap</b> |
| Shielded<br><b>Metal, Non-shielded</b> | No. of Contacts<br><b>N/A</b>           |
| Connector Gender<br><b>Male</b>        | Backshell<br><b>N/A</b>                 |
| Mating Style<br><b>Screw Thread</b>    | IP Rating<br><b>N/A</b>                 |
| Assembly Style<br><b>With Chain</b>    |                                         |
| <span>More Options</span>              |                                         |

### People Also Bought

