

Product Line

DeepTronica

>

Single Pair Ethernet

>

ZConnect

>

Ceres

>

X-Lok

>

- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size

M Series

>

FLOS & FLOS+

>

Power

>

RBL

>

HS-Lok

>

NMEA 2000

>

Heavy Duty Shielded

>

RJ

>

USB

>

SSL

>

HDMI

>

DVI

>

Fiber Optic

>

RF

>

Cable Joiner

>

Cable Gland

>

Pressure Relief Vent

>

LED Light Guide

>

D-Sub

>



BB-02PMMS-QC8001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: UL2238, UL50e

You must login first for view the price

Quantity

-1+

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

-0+

X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

-0+

X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

-0+

X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

-0+

X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

-0+

X-Lok, Standard...
AB-BB02FL-BBBL...
-20°C ~ +80°C

-0+

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 10A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 02
Connector Gender Male	Backshell Circular
Mating Style Push Lock	IP Rating IP68
Assembly Style Solder	
More Options	

People Also Bought

BB-02PMMS-QC8001

CTL-204501

DD-10RFMS-RS8C30

MSAP06FL-SAPFL-...

MSDP04ML-SDPFL-...