

Part Number : [985870014](#)

Product Description : HDX Crimp Terminal, Female,
0.635mm, 24-20 AWG (0.22-0.60mm²);, Tin (Sn)

Series Number : 98587

Status : Obsolete

Product Category : Crimp Terminals



Documents and Resources

Drawings

[985870014 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	98587
Description	HDX Crimp Terminal, Female, 0.635mm, 24-20 AWG (0.22-0.60mm ²), Tin (Sn)
Comments	Only to use within our HDX Connector Family
Product Name	HDX
UPC	800754712934

Physical

Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.253/g
Packaging Type	Reel
Plating min - Mating	2.032µm
Plating min - Termination	2.032µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.20-1.80mm
Wire Size (AWG)	20, 22
Wire Size mm ²	0.32-0.51

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
-------------	-------------

Extraction Tool	<u>638136100</u>
Extraction Tool	<u>638136300</u>
Extraction Handtool	<u>638136500</u>
FineAdjust Applicator for Crimp Receptacle Terminal	<u>639016500</u>

This document was generated on Sep 10, 2026

Obsolete