




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
P	ECN 12067: REVISED NOTES, ADDED NOTE 2 (TORQUE), REVISED FORMAT	09/02/2022	GUTTADAURO



"J1"
SERIES A
USB WATERPROOF JACK

WIRING TABLE	
PIN#	COLOR
1	BLACK (PT BLACK 6C)
2	GREEN (PT 328C)
3	WHITE (RAL 9003)
4	RED (PT 1945C)
SHELL	GREY (PT 421C)



NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
2. SUGGESTED MAX. TORQUE VALUE FOR HEX NUT IS 1.0N-m (8.8 lbf-in)
3. INGRESS PROTECTION RATING IS IP67 (J1 ONLY ,MATED)
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS	DATE	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY C.MCCORMICK	07/29/2003		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CHECKED BY D.PARHAM	08/01/2003		
THIRD-ANGLE PROJECTION 		APPROVED BY R.CARRICK	08/01/2003	CATEGORY USB	PRODUCT DESCRIPTION USB WATERPROOF SERIES "A" BULKHEAD TO BLUNT END
COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. WPUSBAF	REV. P
SCALE: NONE		CAD FILE: WPUSBAF.SLDDRW		SHEET 1 OF 1	