

Johanson Part Number TDCP101W152K1GV001T

Johanson Part Number: TDCP101W152K1GV001T

Johanson Company: JDI

Legacy P/N: 101R14W152KV4T

Size for Capacitors (EIA): 0603

Description: Capacitors SMT, X7R, 0603, 100V, 1500pF $\pm$ 10%, Ni/Sn (RoHS), 7" Reel Paper Tape

Specification Number: None

Life Cycle Stage: EOL

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.035

Schedule B: 8532.24.00.20

Thickness (Min): None

ITAR: No

End Band(Min): 0.01

ECCN: EAR99

End Band (max): 0.015

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 12

Country of Origin: US, MX, or CN

Length (Min): 0.055

Product Family: Capacitors

Length (Max): 0.071

Product Subfamily: Capacitors Surface Mount < 500V

Width (Min):0.024

Capacitance Value: 1500.000

Width (Max): 0.040

Cap Unit of Meas: pF

Part Weight (mg): 8.00

Tolerance: $\pm$ 10%

Packaged Width (lb) Arm: None

Voltage: 100.0

Packaging: 7" Reel Paper Tape

Dielectric Temp Coefficient: X7R

Packaging Qty: None

Termination: 68

Operating Temp Range: -55°C to +125°C

Marking: No Mark

Storage Temp Range (Packaged): +5°C to +40°C with RH 20% to 70%

Product Release Date: Jan. 3, 2006

Storage Temp Range (None Operating): -65°C to +125°C

Harmonization: 8532.24.00.20

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansondielectrics.com/surface-mount-mlc-capacitors>

Printed from: <https://www.johansontechnology.com/part/TDCP101W152K1GV001T/>