

Part Number : [1300390376](#)
Product Description : Mini-Change Terminator,
Female, 5 Pole
Series Number : 130039
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : DN150



Documents and Resources

Drawings

[1300390376_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130039
Description	Mini-Change Terminator, Female, 5 Pole
IP Rating	IP67
Product Name	Mini-Change
Type	Terminator
UPC	78172553529

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	50V AC/DC

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	58.121/g
Orientation	Straight
Poles	5
Temperature Range - Operating	0° to +60°C
Wire Size (AWG)	N/A

This document was generated on Sep 15, 2026