

[Hoods And Covers](#)
[D-Sub Connectors](#)
[Power D/ Combo D](#)
[Modular](#)
[Bel Stewart Connector](#)
[ALTW Waterproof](#)
[Other Products](#)
[New Product](#)


M12 to RJ45 Adaptor

Amphenol LTW introduces M12 to RJ45 ODVA Compliant adaptors which provide a bulkhead style M12 connector on one and a shielded RJ45 jack on the other end to address specific Industrial Ethernet applications

[Click here for more information...](#)

Our Latest Catalogue



[Click here for more information...](#)



MHED-M-SERIES – Jackscrew



[Click Image for a Bigger Picture](#)

Technical Specification

Operating Temperature	-55°C to +110°C
Cable Entry	Top
Material	UL recognised plastic material
Jackscrew	UNC 4-40, male and female versions
Cable Diameter	Up to 9mm
Plating	Nickel over Copper

Main Features

- Suitable for sizes 9, 15, 25, 37 way
- Easy to re-open
- Male or female jackscrew
- External cable clamp

Ordering

Size	Part Number	Product Code	Size
9-way	2801-0106-01	MHED-MD09T-K	Male
15-way	2801-0106-02	MHED-MD15T-K	Male
25-way	2801-0106-03	MHED-MD25T-K	Male
37-way	2801-0106-04	MHED-MD37T-K	Male
9-way	2801-0106-11	MHED-MD09TF-K	Female
15-way	2801-0106-12	MHED-MD15TF-K	Female
25-way	2801-0106-13	MHED-MD25TF-K	Female
37-way	2801-0106-14	MHED-MD37TF-K	Female



Catalogue

Data sheet