

Vertical type plastic backshell (with screw lock) PCR-LS()LA()

1.27 mm pitch connectors

Backshell

Vertical type



● Configuration of product Part No.

PCR-LS () LA()

① ② ③


- ① Series name
- ② No. of contacts: 20, 28, 36 or 50
- ③ Vertical type backshell for PCR-S()F, PCR-S()FS

PCR-LS20LA1: Max outside diameter of cable is 10 mm.
 PCR-LS20LA : Max outside diameter of cable is 10 mm.
 PCR-LS28LA : Max outside diameter of cable is 14.5 mm.
 PCR-LS36LA : Max outside diameter of cable is 15 mm.
 PCR-LS50LA : Max outside diameter of cable is 16 mm.

PCR-LS20LA1

● Components


①	Housing
②	Lock hardware
③	Screw lock
④	Clamp



PCR-LS36LA

● Components


①	Housing
②	Lock hardware
③	Screw lock
④	Clamp



PCR-LS20LA

● Components


①	Housing
②	Lock hardware
③	Screw lock
④	Clamp



PCR-LS50LA

● Components


①	Housing
②	Lock hardware
③	Screw lock
④	Clamp



PCR-LS28LA

● Components

①	Housing
②	Lock hardware
③	Screw lock
④	Clamp



Mating connectors: PCR-E20F(), PCR-E20FS