

KLK010 - KLK Series



Series: KLK Series

KLK Series Datasheet

- Fast-acting, high-interrupting capacity, current-limiting type fuse.
- Especially suited for control circuits, street lighting, H.I.D. lighting, computers, and other applications without high inrush currents.

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

Product Literature

[KLK Series Datasheet](#)

[KLK Series Time Current Curves](#)

[KLK Series 3D Model IGS](#)

[KLK Series CAD Drawing DXF](#)

NEW POWR-Gard Products Catalog

DOWNLOAD

Download Literature App!

Click here to download the app!

Electrical Characteristics	Technical Resources	Environmental Info
Property (Mouseover for details)	Value	
Ampere Rating (A)	10	
VAC (V)	600	
VDC (V)	500	
Interrupting Rating	100000A@600VDC	
Opening	Fast-Acting (F)	
Package Size	Midget/5AG	

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).



- About Littelfuse
- [About Littelfuse](#)
- [Conflict Free Statement](#)
- [History](#)
- [Investor Relations](#)
- [Legal](#)
- [Press Room](#)
- [Privacy Statement](#)

- Explore Littelfuse
- [Capabilities Brochures](#)
- [Careers](#)
- [Check Distributor Stock](#)
- [Competitor Cross Reference](#)
- [Industries](#)
- [Order Samples](#)
- [Products](#)

- Technical Resources
- [Application Designs](#)
- [Education](#)
- [FAQs](#)
- [iDesign™](#)
- [Littelfuse University](#)
- [Product Catalogs](#)
- [Quality Documents](#)

Feedback

