

Color :  White

UPC Code : 078477712559

Country Of Origin : China

NEMA :  5-15R

Available Colors :



GFNT1-W

15 Amp, Self Test, Non Tamper-Resistant Slim GFCI Outlet with LED Indicator Light

15 Amp, 125 Volt Receptacle/Outlet, 20 Amp Feed-Through, Self-test SmartlockPro Slim GFCI, monochromatic, back and side wired, nylon wallplate/faceplate and self grounding clip included - White

- SAFE – Delivers continuous ground fault protection
- SELF TESTING – Automatically self-tests to ensure it can respond to ground fault
- SIMPLE – Status indicator light provides simple, intuitive feedback
- COMPATIBLE – Device designed to improve immunity for reduced HF nuisance tripping

Technical Information

Electrical Specifications

Amperage : 15 A

Dielectric Voltage : 1250 VAC

Grounding : Self-Grounding

Horsepower Rating : 1 hp

Pole(s) : 2

Power Supply Input and Frequency : 125V, 60Hz

Short Circuit Current Rating :
10 kA

Temperature Rise : Max 30°C

Trip Level : Class A

Voltage : 125 VAC

Wire(s) : 3

Environmental Specifications

Operating Temperature :
Maximum Continuous 66°C,
Minimum -35°C (w/o impact)

Material Specifications

Body : Thermoplastic

Face : Thermoplastic

Grounding Screw : #8
Galvanized Steel

Line Contacts : Brass

Mounting Strap : Galvanized
Steel

Self-Grounding Clip : Yes

TR Shutter : Non-Tamper

Terminal Clamps : Brass

Terminal Screws : #8 Plated
Steel

Mechanical Specifications

Product ID : Ratings are
marked on device

Termination : Back and Side
Wire

Torque Range : 14-18 lbs.

Wire Accomodation : #10 -
#14 AWG Copper, #10 - #12
Copper Clad

Product Features

Brand : SmartlockPro

Color : White

Device Type : Duplex
Receptacle/Outlet

Feature(s) : Indicator Light,
Self-Test

Grade : Residential
/Commercial Specification
Grade

NEMA Configuration : 5-15R

Product Type : GFCI

Standards and Certifications

**Applicable Standards and
Certifications :** UL|CSA|CSA
C22.2 No. 144|CSA C22.2 No.
42|Fed Spec WC-596|UL
943|UL 498

NEMA : WD-1 and WD-6

Warranty

Warranty : 2-Year Limited

Features and Benefits

- Provides continuous ground fault protection – detects and trips on actual ground fault even when self-test is being conducted
- On initial power up, tests the GFCI within 3 seconds
- Auto-monitoring exceeds the UL requirement
- Auto adapts and shifts to more frequent testing if potential problem is detected
- Status Indicator Light provides simple, intuitive feedback on power and protection status as well as indication of line/load reversal
- Patented Lockout Action prevents reset if GFCI is damaged and cannot respond to a ground fault
- Electronics are designed to minimize any false triggers
- Reduced depth makes it easier to install in any electrical box, even shallow ones
- Terminals allow for easy wiring options – back and side wire capable
- External back wire clamps provide visual indication of proper wire seating
- Withstands high torque and resists wire pullout
- Standard brass self-grounding clip
- Trip threshold meets or exceeds UL requirements for tripping time
- Improved immunity to high-frequency noise reduces nuisance tripping
- Advanced electronics design provides superior resistance to electrical surges and over-voltages
- Compatible with all Decora devices and wallplates; available in select Decora colors
- UL Fed Spec WC-596 rated.

Patents *

CA2730014

MX308495

US10483066

MX302458


MX344697

US11456138

US7697252	US8587914
US8599522	US8944859
US9053886	US9276393

This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

Dimensional Drawing



SPECIFICATION SUBMITTAL

JOB NAME: 	CATALOG NUMBERS: 	
JOB NUMBER: 		

Leviton Manufacturing Co., Inc

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.
T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-461-2002 ·
FAX: +1-800-824-3005 ·

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)
5386- 1797 ·

Visit our Website at: www.leviton.com

© 2026 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without
notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/company/about-leviton/locations

© 2026 Leviton Manufacturing Co., Inc.