

LUMOTAST FK/25, female quick connector



Description

The 4-pole female connector is perfectly matched to the RAFI ribbon cable. The insulation displacement connector makes contact with the wires when the strip parts are pressed together.

The female connector is equipped with insulation displacement connectors for contacting 4-pole cables.

technical data

> general

Color	light gray
Operating temperature, min.	-65 °C
Operating temperature, max.	105 °C
Packaging unit	50 pcs.
Net weight	0.7 g
Minimum order quantity (MOQ)	50 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Country of origin	FR

direct links

> [RAFI eCatalog](#)

> mounting diameters

Outside dimension, length	7 mm
Outside dimension, width	9.55 mm
Outside dimension, height	10.6 mm

> electrical data

Rated voltage, min.	0.02 V
Rated voltage, max.	25 V
Rated current, min.	0.0001 A
Rated current, max.	0.1 A
AWG max.	28 mm ²
AWG min.	26 mm ²