

SATO PARTS CO.,LTD. > Product Category > Screwless Terminal Blocks

- Product mass
- Precautions for use
- General notes

SL-4000-CWJH

made in JAPAN



- Pitch 3.81mm
- 2-pieces (Separate type)

 R50270956 

Order model number

- Order model numberSL-4000-CWJH-[Position]GY
- Order exampleSL-4000-CWJH-2PGY (An example of ordering with 2 positions.)

- Basic information
- Dimension
- Soldering heat resistance conditions
- Optional
- Conformity product / Mate product
- Download

[SL-4000series Video \(Play on YouTube\)](#)

Basic information

Rating		Add to My List >	Sample request (Only available in Japan) >
		300V-5A	
Insulation resistance	DC500V、100MΩ Min		
Withstand voltage	AC2000V (1minute)		
Certificates & Approvals	TÜV (Compliant with IEC61984)		
Position	2、3、4、5、8、10、12		
Main insulator	Nylon66 (UL94V-0)		
Terminal type	PC terminal		
Body color	GY (Gray)		
Overview	1.It is a product only on the receptacle side of SL-4000-CWSH.		
Note	1.It is recognized as a UL or CSA (C-UL) approved product when used with a plug.		

- Home
- Product search
- Product Category
- About SATO PARTS
- News classification
- Contact us
- Video channel
- Download brochure
- Environmental initiatives
- Privacy policy
- Cookie policy
- Download terms

Terms of Use