


[home](#) > [Products](#) > [Screwless Terminal Block](#) > ML-700-NH

Search

Search

Products

[Audio,Video](#)
[Connectors/Pin Plug Jack](#)
[Bushing/Grommet](#)
[Chip Jack/Banana Jack](#)
[Clip](#)
[Fuse Holder](#)
[L.E.D. Indicator](#)
[Metal Knob](#)
[Neon Indicator](#)
[Non inventory product](#)
[Plastic Knob](#)
[Screw Terminal Block](#)
[Screwless Terminal Block](#)
[Solder Lug](#)
[Terminal/Connector](#)



Click image to enlarge



ML-700-NH

Screwless Terminal Block

Screwless Terminal Block

Screwless Terminal Block

Product ID: P6YRI4

Availability: Usually Ships in 3 to 5 Days

Pitch : 2.54 mm

UL : E101073

CSA : 65928

TÜV : J 2050667

RoHS : RoHS Compliance

Overview

Soldering Condition

Size Table

Technical Description

Rating	50V-3A
Insulation resistance	DC500V, 50MΩ Min
Withstand voltage	AC1500V 1 minute
certificates & approvals	UL(Approved for field wiring), CSA, TÜV (IEC60947-7-1)
Position	2 ~ 20
Check hole	On top
Main insulator	Nylon 66 (UL94V-0)
Button insulator	P.P.E. (UL94V-0)
Rating wire	Solid Wire :Φ0.65mm (AWG22), Stranded Wire :0.32sq mm (AWG22)
Range of wire	Solid Wire :Φ0.32mm~Φ0.65mm (AWG28~AWG22) Stranded Wire :0.08sq mm ~ 0.32sq mm (AWG28~AWG22)
Terminal type	PC terminal
Wire Strip Length	9~10mm (0.355~0.394 inch)
Body color	GY (Gray)
Button color	W (White)
Applicable tool for button	Screw driver or others
Caution	1.Don't immerse and wash this product in liquid. 2.We recommend that you download the product documents "mm-inch conversion chart" before you purchase this product.