

**MODEL:** PJ-002AH-SMT-TR | **DESCRIPTION:** DC POWER JACK**FEATURES**

- high current rating: 5 A
- internal switch
- RoHS compliant


**SPECIFICATIONS**

| parameter                  | conditions/description | min | typ   | max | units  |
|----------------------------|------------------------|-----|-------|-----|--------|
| rated input voltage        |                        |     | 24    |     | Vdc    |
| rated input current        |                        |     |       | 5.0 | A      |
| contact resistance         |                        |     |       | 30  | mΩ     |
| insulation resistance      | at 500 Vdc             | 100 |       |     | MΩ     |
| voltage withstand          | for 1 minute           |     |       | 500 | Vac    |
| insertion/withdrawal force |                        | 0.3 |       | 3   | kg     |
| operating temperature      |                        | -25 |       | 85  | °C     |
| life                       |                        |     | 5,000 |     | cycles |
| flammability rating        | UL94V-0                |     |       |     |        |
| RoHS                       | yes                    |     |       |     |        |

**SOLDERABILITY**


| parameter        | conditions/description                                                                            | min | typ | max | units |
|------------------|---------------------------------------------------------------------------------------------------|-----|-----|-----|-------|
| reel storage     | -5~35°C, 25~80% humidity<br>reel opened: use within 1 month<br>reel unopened: use within 6 months |     |     |     |       |
| reflow soldering | see reflow profile                                                                                |     |     | 260 | °C    |

Note: 1. Same Sky recommends usage of the product within 2 hours after T&R is opened. After 6 hours, Same Sky recommends drying the parts prior to use.







MECHANICAL DRAWING



units: mm  
tolerance:  
X,  $\pm 0.50$  mm  
X.X  $\pm 0.30$  mm  
X.XX  $\pm 0.20$  mm  
PCB:  $\pm 0.05$  mm  
unless otherwise specified  
PCB thickness: 1.6 mm



| DESCRIPTION | MATERIAL        | PLATING/COLOR |
|-------------|-----------------|---------------|
| center pin  | copper          | nickel        |
| terminal 1  | brass           | silver        |
| terminal 2  | copper alloy    | silver        |
| terminal 3  | brass           | silver        |
| housing     | PA10T (UL94V-0) | black         |
| cover       | PA10T (UL94V-0) | black         |



Recommended PCB Layout  
Top View



MATING PLUG


Jack Insertion Depth: 9.5 mm

|            |                      |
|------------|----------------------|
| SCHEMATIC  |                      |
| Model      | PJ-002AH-SMT-TR      |
| Center Pin | $\varnothing 2.0$ mm |

PACKAGING

units: mm

Reel Size: Ø330 mm  
Reel QTY: 300 pcs per reel



REVISION HISTORY

| rev. | description                                                              | date       |
|------|--------------------------------------------------------------------------|------------|
| 1.0  | initial release                                                          | 10/19/2005 |
| 1.01 | updated operating temperature                                            | 06/17/2011 |
| 1.02 | added jack insertion depth                                               | 09/13/2012 |
| 1.03 | added TR package option                                                  | 11/28/2012 |
| 1.04 | increased voltage rating                                                 | 04/28/2016 |
| 1.05 | added storage and drying conditions, and tape and reel packaging details | 10/13/2017 |
| 1.06 | brand update                                                             | 10/30/2019 |
| 1.07 | logo, datasheet style update                                             | 08/05/2022 |
| 1.08 | updated tape and reel packaging                                          | 06/19/2023 |
| 1.09 | manufacturing improvement changes                                        | 08/29/2024 |
| 1.10 | CUI Devices rebranded to Same Sky                                        | 09/12/2024 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**