


Data sheet Product SLM N 1 092 10 G


[PRINT DATA SHEET](#)
[RECOMMEND PAGE](#)


PCB connectors>Male headers
Straight, narrow insulator,
suitable for female header BLM, one row 1-20 contacts

Features

grid:	1.27 mm
no. of contacts:	10
contact material:	CuZn-alloy
surface of contact:	gold-plated
surface contact / contact sleeve:	- Ni+≥0.2µm Au - Ni+4...6µm Sn
version:	narrow insulator
volume resistance:	≤5 mΩ
nominal current:	1.5 A
nominal voltage:	125 V AC
test voltage:	300 V
insulating body material:	PA 4.6. GF
temperature range:	-40°C... +163°C (260°C/10 s)
class of inflammability:	UL 94 V-0
specific insulation resistance:	>10 ⁷ Ω·m
connection type:	THT (soldering)
reflow solderable:	yes

Technical Drawing



A:	14 mm
B:	3.1 mm
C:	9.2 mm