

Pressure Switch - 76074 (/sensing.honeywell.com/product-page?pr_id=)

([Home \(/\)](#) : [Products \(/products\)](#) : [Switches](#) : [Pressure and Vacuum Switches](#) : [Pressure Switch](#) : 5000)

Distributor Inventory

Input part number for stock availability



5000 Series pressure switch with standard terminal

Actual product appearance may vary.

Sales & Service

Distributor Inventory

Overview **Specs** Documentation

Product Specifications

Product Type	Pressure Switch
Electrical Termination	#8-32 screw
Contact Setting Range	51 psi to 90 psi, ±7 psi
Standard Factory Set Points	60 psi, 75 psi, & 80 psi
Circuitry	NO/NC, adjustable
Contact(s)	Silver alloy, gold plated
Proof Pressure	500 psi
Burst Pressure	1250 psi
Operating Pressure	250 psi
Resistive Ratings	15 A, 6 Vdc; 8 A, 12 Vdc; 4 A, 24 Vdc
Inductive Ratings	1 A, 120 Vac; 0.5 A, 240 Vac
Standard Seal	Nitrile O-ring
Diaphragm	Polymide film
Temperature	-40 °F to 250 °F
Base	Plated steel
Cover Type	Glass reinforced polyester
Options	Brass, plastic, or stainless steel base; various base connector thread sizes; wire leads (potted and sealed)
Connector(s)	1/8-27 NPT male thread
Availability	Global
Series Name	5000

Narrow Your Search

Modify Your Search

Products

Select Option

Technology

Select Option

Industries Served

Select Option

Product Search

Product Type:

All Product Types

Industry:

All Industries

☐ New Products Only

☒ Entire Product Catalog

My Links

eCOM Login (/index.php?ci_id=50629&la_id=1)
Request Access to eCOM (/ecom-access-request)
Rep/AD Portal Login (/index.php?ci_id=50606&la_id=1)
Rep/AD Portal Access Request (/index.php?ci_id=50630&la_id=1)
Sample Request (/samplerequest)
Digital U - HWL Learning Hub Login (/index.php?ci_id=50607&la_id=1)
Limitless Microsite (/index.php?ci_id=50631&la_id=1)
Supplier Microsite (/index.php?ci_id=44887&la_id=1)

Literature and Media

[Data Sheets \(/white-paper-and-technical-data-sheets-library2\)](#)
[Videos \(/videos\)](#)
[Literature \(/literature\)](#)
[Literature Request \(/index.php?ci_id=50636&la_id=1\)](#)
[White Papers \(/whitepapers\)](#)
[Application Notes \(/application-notes\)](#)
[Application Demos \(/index.php?ci_id=141383&la_id=1\)](#)
[CAD Renderings \(/cad-renderings\)](#)

Contacts

Customer Service (/index.php?ci_id=50608&la_id=1)
 Technical Support (/index.php?ci_id=50609&la_id=1)
 Global Sales & Service (/index.php?ci_id=50610&la_id=1)



CHAT

CHAT