





HARDWARE:



Compliance: RohS III (2015/863/EU)

|                                           |       |      |                |      |            |          |      |
|-------------------------------------------|-------|------|----------------|------|------------|----------|------|
| Tolerances: 0.00: ±0.25mm<br>0.0: ±0.40mm |       |      | Date           | Name | DPW 1 AG-x |          |      |
|                                           |       |      | 03/09          | dr   |            |          |      |
|                                           |       |      |                |      |            |          |      |
|                                           |       |      |                |      |            |          |      |
| Accessory                                 | 10/19 | dr   | knitter-switch |      |            | 30 17 62 | Page |
| Rating, electrical life                   | 02/13 | dr   |                |      |            |          | 1/2  |
| Dimensions                                | 06/10 | dr   |                |      |            |          |      |
| Modifications                             | Date  | Name |                |      |            |          |      |

Specifications:

Contact rating: max. 100mA, 24V DC - endurance 200 000 cycles  
max. 2A, 125VAC - endurance 10 000 cycles

Contact resistance: 100mOhm max.

Insulation resistance: 1GOhm min. at 500V DC

Dielectric strength: 1 000V AC RMS

Operating force: 4.5 - 6.5N

Torque: 1.5Nm max. applied to nut

Soldering conditions: 350°C max., 5sec.

Panel thickness: min.: 1.5mm; max.: 4.0mm

Total travel: 2.5mm

Switching function: off - on

Contact bounce: 10ms

Material: Case / cap / bushing: polyamide 6/6  
Terminal / contact: gold over silver plated

IP rating: IP 67 (mounted)

| X=CAP COLOR |        |
|-------------|--------|
| W           | white  |
| K           | black  |
| R           | red    |
| O           | orange |
| Y           | yellow |
| G           | green  |
| B           | blue   |

Compliance: RohS III (2015/863/EU)

|                                           |       |      |                |      |            |      |
|-------------------------------------------|-------|------|----------------|------|------------|------|
| Tolerances: 0.00: ±0.25mm<br>0.0: ±0.40mm |       |      | Date           | Name | DPW 1 AG-x |      |
|                                           |       |      | 03/09          | dr   |            |      |
|                                           |       |      |                |      |            |      |
|                                           |       |      |                |      |            |      |
|                                           |       |      |                |      |            |      |
| Accessory                                 | 10/19 | dr   | knitter-switch |      | 30 17 62   | Page |
| Rating, electrical life                   | 02/13 | dr   |                |      |            | 2/2  |
| Dimensions                                | 06/10 | dr   |                |      |            |      |
| Modifications                             | Date  | Name |                |      |            |      |