



Pushing Performance
Since 1945

cable clamp metal hood 9-37P dia. 9-12mm



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 000 0143
Specification	cable clamp metal hood 9-37P dia. 9-12mm
HARTING eCatalogue	https://harting.com/61030000143

Identification

Category	Accessories
Type of accessory	Cable clamp
Description of the accessory	D-Sub 1 ... 4

Technical characteristics

Ambient temperature	-20 ... +90 °C
Cable diameter	9 ... 12 mm

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	10
Net weight	17.5 g
Country of origin	China



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85389099
GTIN	5713140157255
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400