

GP 125 Cover

Industrial Plug and Socket Accessorie

2CMA164999R1000

Protective cover, rated current 125A, 2-poles+earth, 3-poles+earth and 3-poles+neutral+earth



GENERAL

Product Name	Industrial Plug and Socket Accessorie
Product ID	2CMA164999R1000
Function	Protective cover, 125 A, IP 44/67
EAN	7392696649995
Catalog Description	Protective cover, 125A, 2P+E, 3P+E and 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2409590
E-Number Norway	2417557
E-Number Sweden	E2417557
Standards	IEC 60309-2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	100 millimetre
Product Net Height	43 millimetre
Product Net Length	365 millimetre
Product Net Depth	365 millimetre
Product Net Weight	0.06 kilogram

TECHNICAL

Product Main Type	Accessory
Color	
Number of Poles	5
Clock Position	
Rated Current	125 ampere
Rated Voltage	
Frequency	
Degree of Protection	IP67
Cable Cross-Section	
Housing Material	
Plug Angle	
Product Group	Accessories

PACKAGING

Package Width	100 millimetre
Package Height	43 millimetre
Package Gross Weight	0.06 kilogram
Package Length	365 millimetre
Package Units	box 1 piece