

4280	5280	0479	0379
4280-0-XX-XX-16-XX-10-0 Solder mount in $\varnothing 1,7 \pm 0,08$ PTH. #16 Contact for $\varnothing 0,56-0,86$ pins. Also available on 8mm wide carrier tape: 6,000 parts per 330mm reel.	5280-0-XX-XX-16-XX-40-0 Solder mount in $\varnothing 1,7 \pm 0,08$ PTH. #16 Contact for $\varnothing 0,56-0,86$ pins. Also available on 16mm wide carrier tape: 2,200 parts per 330mm reel.	0479-0-XX-XX-34-XX-10-0 Solder mount in $\varnothing 1,96 \pm 0,08$ PTH. #34 Contact for $\varnothing 0,81-1,17$ pins. Also available on 16mm wide carrier tape: 2,000 parts per 330mm reel.	0379-0-43-XX-34-XX-10-0 Solder mount in $\varnothing 1,96 \pm 0,08$ PTH. #34 Contact for $\varnothing 0,81-1,17$ pins.
9873	5364	5291	3966
9873-0-XX-XX-02-XX-10-0 Solder mount in $\varnothing 2,11 \pm 0,08$ PTH. #02 Contact for $\varnothing 1,02-1,27$ pins. Also available on 12mm wide carrier tape: 4,500 parts per 330mm reel.	5364-0-XX-XX-23-XX-10-0 Solder mount in $\varnothing 2,62 \pm 0,08$ PTH. #23 Contact for $\varnothing 1,14-1,65$ pins. Also available on 12mm wide carrier tape: 2,000 parts per 330mm reel.	5291-0-XX-XX-08-XX-40-0 Solder mount in $\varnothing 3,53 \pm 0,08$ PTH. #08 Contact for $\varnothing 2,13-2,59$ pins. Also available on 16mm wide carrier tape: 1,700 parts per 330mm reel.	3966-0-XX-XX-07-XX-10-0 Solder mount in $\varnothing 3,43 \pm 0,08$ PTH. #07 Contact for $\varnothing 1,65-2,08$ pins. Also available on 24mm wide carrier tape: 650 parts per 330mm reel.
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT SOLDER BARRIER: Organic Fibre Plug® DIMENSION IN INCHES TOLERANCES ON: LENGTHS: $\pm 0,13$ DIAMETERS: $\pm 0,05$ ANGLES: $\pm 2^\circ$ ORDER CODE: XXXX - 0 - XX - XX - XX - XX - X0 - 0 BASIC PART # → SPECIFY PACKAGING: → 43 Discrete Receptacles 67 Supplied on 330mm Reels SPECIFY SHELL FINISH: → 01 5,08µm TIN/LEAD OVER NICKEL 80 5,08µm TIN OVER NICKEL ◇ SPECIFY CONTACT FINISH: → 27 0,76µm GOLD OVER NICKEL ◇ 01 5,08µm TIN/LEAD OVER NICKEL 80 5,08µm TIN OVER NICKEL ◇ CONTACT # → #02, #07, #08, #16, #23 or #34 CONTACT (DATA ON PAGES 221 - 226)			