




**MOUNTING HOLE LAYOUT
(TOP VIEW)**

Dimensions and Hole Specifications:

- Horizontal dimensions (from left edge):
 - .386 [9.80]
 - .315 [8.00]
 - .256 [6.50]
 - .157 [3.99]
- Vertical dimensions (from top edge):
 - .295 [7.49]
 - .209 [5.30]
- Hole Specifications:
 - .078 [1.98] DIA. HOLE (2) PLS
 - .082 [2.08] DIA. HOLE (3) PLS
 - .090 [2.87] DIA. HOLE
- Feature Callouts:
 - 1: Pin 1 (bottom-left)
 - 3: Pin 3 (bottom-right)
 - 4: Pin 4 (bottom-right)



SCHEMATIC



PART NO.	COLOR
970	WHITE
971	RED
972	BLACK
973	YELLOW

- ① EARTH TERMINAL: .020 [0.5] TH'K BRASS
NICKEL PLATE
- ③ SPRING: .012 [0.3] TH'K
PHOSPHOR BRONZE
SILVER PLATE
- ④ CONTACT: .016 [0.4] TH'K BRASS
SILVER PLATE

970-973

4.1.03 CHANGE AS PER ECN 03-026

A

DATE _____

DESCRIPTION

REV.