

Accessories
PROTECTIVE CAP, N, jack (female)
62_N-0-0-1/--3_-

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP68
- Interface dimensions according IEC/MIL



General data	
Technology	Radio Frequency
Weight	0.012 kg
Body material	Brass / SUCOPLATE (R) Plating
Gasket material	VMQ (Silicone rubber)
Fastening nut material	Brass / SUCOPLATE (R) Plating
Operation temperature	-65 °C ... 165 °C
Remarks	length of chain: 115 mm

Ordering Information Table	
Item number	Item description
22543433	62_N-0-0-1/--3_-E

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31328 / Date of publication: 22.08.2025 / uncontrolled copy