

Exhaust Filters *PFA4 Series*

Type 12



- Maintains a UL-tested NEMA Type 12 seal, ensuring reliable protection against dust, dirt, and non-corrosive liquids.
- UL Recognized (UL 508, NITW2/8) and CSA Certified for trusted compliance.
- Patented “Click & Fit” design enables fast, tool-free installation with no hardware required.
- Constructed from high-strength, heat-resistant ABS-FR, rated UL 94 V-0 for superior flame resistance.
- Fluted, heavy-duty filter delivers extended service life, lasting up to 3× longer than standard filter materials.
- Available in RAL7035 Light Gray or RAL9011 Black to suit a variety of enclosure styles.



Gallery



Accessories

- Replacement Filters

Part Number Light Gray (RAL7035)	Part Number Black (RAL9011)	Filtration Efficiency %
PFA10000LG	PFA10000BK	88
PFA20000LG	PFA20000BK	91
PFA30000LG	PFA30000BK	91
PFA40000LG	PFA40000BK	91
PFA60000LG	PFA60000BK	91

