

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >

- Middle Size
- Large Size
- ODVA
- Accessory

- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >




RCP-5SPFFH-SSU7001

Operating Temperature: -40°C ~ +105°C
Transmission Speed: Cat 5e
Shielded: Plastic, Shielded
Jacket Material: N/A
Certificate: N/A

You must login first for view the price

Quantity - 1 +

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type ▼ Search



Ceres, Accessory...
CAP-WACMSMA1
-40°C ~ +105°C

- 0 +

☐



Ceres, Accessory...
CAP-WACMSPB1
-40°C ~ +105°C

- 0 +

☐



Ceres, Accessory...
CAP-WACMSPC1
-40°C ~ +105°C

- 0 +

☐



Ceres, Accessory...
CAP-WACMSPD1
-40°C ~ +105°C

- 0 +

☐



Ceres, Accessory...
CAP-WACMSPD2
-40°C ~ +105°C

- 0 +


☐



Ceres, Accessory...
TOL-152501
N/A

- 0 +

☐

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Receptacle
Shielded Plastic, Shielded	No. of Contacts N/A
Connector Gender Jack	Backshell Square
Mating Style Screw Thread	IP Rating IP67
Assembly Style Jack 180° (Horizontal)	
	

People Also Bought

- 

RCP-5SPFFH-...
- 

BD-02BMFA-QLBMN0
- 

MSAS08ML-SASML-...
- 

1CD-08BMFM-LL6A03
- 

MSAP12FL-SAPFL-...