

SUNON®

Mighty Mini Fan & Blower

*All products are RoHS compliant.



Dustproof & Waterproof



Halogen Free



10x10x3 mm


12x12x3 mm

15x15x3 mm

17x17x3 mm

Mighty Mini Fan

Size (mm)	Model (IP55)	Model (IP58)	Rating Voltage (V)	Operating Voltage (V)	Power Current (mA)	Power Consumption (Watts)	Speed (RPM)	Air Flow (l/min)	Static Pressure (Pa)	Noise (dB(A))
10x10x3	UF3A3-500	UF3A3-500B	3	2.0-3.5	96	0.29	17000	3.43	10.44	21.0 / 30cm
	UF3A3-700	UF3A3-700B								
12x12x3	UF3C3-500	UF3C3-500B	3	2.0-3.5	97	0.30	16500	5.95	18.91	28.3 / 20cm
	UF3C3-700	UF3C3-700B								
15x15x3	UF3F3-500	UF3F3-500B	3	2.0-3.5	36	0.10	14500	8.75	20.36	30.0 / 30cm
	UF3F3-700	UF3F3-700B								
17x17x3	UF3H3-500	UF3H3-500B	3	2.0-3.5	37	0.10	13000	16.27	21.21	32.0 / 30cm
	UF3H3-700	UF3H3-700B								



9x9x3 mm

12x12x3 mm

15x15x3 mm

17x17x3 mm

30x30x3 mm

Mighty Mini Blower

Size (mm)	Model (IP55)	Model (IP58)	Rating Voltage (V)	Operating Voltage (V)	Power Current (mA)	Power Consumption (Watts)	Speed (RPM)	Air Flow (l/min)	Static Pressure (Pa)	Noise (dB(A))
9x9x3	UB393-500	UB393-500B	3	2.0-3.5	92	0.28	17400	1.17	16.17	25.0 / 30cm
	UB393-700	UB393-700B								
12x12x3	UB3C3-500	UB3C3-500B	3	2.0-3.5	36	0.10	15500	2.67	22.96	26.0 / 30cm
	UB3C3-700	UB3C3-700B								
15x15x3	UB3F3-500	UB3F3-500B	3	2.0-3.5	38	0.10	14000	4.53	33.85	30.0 / 30cm
	UB3F3-700	UB3F3-700B								
17x17x3	UB3H3-500	UB3H3-500B	3	2.0-3.5	37	0.10	12500	6.50	40.34	32.0 / 30cm
	UB3H3-700	UB3H3-700B								
30x30x3	UB5U3-500	UB5U3-500B	3	2.0-6.0	72	0.36	9500	18.00	88.18	36.0 / 30cm
	UB5U3-700	UB5U3-700B								

※ If you need special specification. Please contact SUNON sales.

※ Specifications are subject to change without notice. Specifications in this catalog are for reference.

※ More SUNON products information please visit SUNON website at www.sunon.com.



Sunonwealth Electric Machine Industry Co., Ltd.

URL : www.sunon.com

email : sunon@email.sunon.com.tw

2015/04/30 (223-E)