

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

FLOS & FLOS+ >

Y series C size

Accessory

B Series A Size

B Series B Size

B Series C Size

B Series D Size

K Series B Size

K Series C Size

K Series D Size

Y Series B Size

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >

ALTW Emporium >



SLKC-03EGFS-GCP-001

Operating Temperature: -40°C ~ +125°C

Transmission Speed: N/A

Shielded: Metal, Shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

 Search



FLOS & FLOS+...
CAP-WLKFGME3
-40°C ~ +125°C

- 0 +

☐



FLOS, K Series C...
FLKC-03FGMS-...
-40°C ~ +125°C

- 0 +

☐



FLOS+, K Series C...
SLKC-03FGMS-...
-40°C ~ +125°C

- 0 +

☐

 Add to Cart

 Inquiry

Specifications

Download / CAD

Nominal Current
12A

Connector Type
Receptacle

Shielded
Metal, Shielded

No. of Contacts
03

Connector Gender
Female

Backshell
Circular

Mating Style
Push Pull

IP Rating
IP68

Assembly Style
Solder

 [More Options](#)

People Also Bought



SLKC-03EGFS-GCP-...



M12A06MR-12AFR-...



CB-02AFFM-RL7A05



DC-02RFMS-RS8D10



MSBP-058MMM-...