

Web site: [www.marinco.com](http://www.marinco.com)

Phone: 800-307-6702


Date: April, 2011

Rev: 02

Connector, straight  
15A, 250V

### **Catalog Number: 320IEC15**

- Item:** Connector, appliance coupler.  
IEC 60320 standard sheet C15.
- Rating:** For hot conditions (120°C rating).  
10 amperes, 250 volts ac: International.  
15 amperes, 250 volts ac (max): North America.
- Materials:** Plastic parts are heat stabilized nylon with CTI greater than 400 volts.  
Contacts are solid brass.
- Contacts:** One piece, .032" thick brass, double wipe.
- Terminals:** Tempered brass, lug style, Perma-Lock™ design.
- Terminal Identification:** Terminal screws are color coded.  
Wire entrance holes marked "L", "N" and "⊥".
- Cord Clamp:** Internal. Accommodates 0.300" (18/3 SJ) to 0.655" (12/3 S) North American cable, and 3 conductor .75 to 4.00 mm<sup>2</sup> harmonized cable.
- Overall Design:** Two assembly screws, U-drive style.  
All screws are combination slot/cross head.  
Beveled housing. Dust seal at cord entry.  
Cable strip length gauge molded into connector body.
- Listings:** UL listed, CSA certified.
- Dimensions:**



Dimensions shown in inches

