





Material	AISI 316L Stainless steel (1,5 mm thick) buttons with built-in silicone rubber sealing gasket
Button stroke	0,6 mm +/- 0,1 mm
Actuation force	4,0 N (typical)
Life expectancy	>3.000.000 cycles
IP Protection rate	IP65
Impact Protection Rate	IK08
Contact technology	Stainless steel metal dome on Gold plated PCB
Contact resistance	<30 Ohm (Vmax=12Vdc; Imax=20mA)
Insulation resistance	>500K Ohm (Vmax=12Vdc; Imax=20mA)
Connection	N.O. contact on 2 pins connector
Operating temperature	-25°/+85°C
Storage temperature	-25°/+85°C

Tolerances: >0-6: ±0.05 mm >6-30: ±0.1 mm >30-120: ±0.15 mm			Date	Name	YME IP 01 B		
			06/12	dr			
Revised	06/21	dr			knitter-switch 30 26 53 Page 1/1		
IP rating	05/19	dr					
Rename	02/14	dr					
Rename	11/13	dr					
Modifications	Date	Name					