

Johanson Part Number LRC0603CS3N9GV001T

Johanson Part Number: LRC0603CS3N9GV001T	Johanson Company: JTI
Legacy P/N: L-14C3N9SV4T	Size for Capacitors (EIA): None
Description: Ceramic Inductor, 0603, 3.9nH±0.3nH, 300mA, Ni/Sn (RoHS), No Mark, 7" Reel Paper Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.039
Schedule B: 8504.50.40.00	Thickness (Min): 0.023
ITAR: No	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.016
RoHS Compliance: Yes, RoHS 10/10	Standard Item: No
REACH: Yes	Lead Time Typical (Weeks)*: 16
Country of Origin: TW	Length (Min): 0.057
Product Family: Inductors	Length (Max): 0.069
Product Subfamily: Ceramic Inductors	Width (Min):0.023
Capacitance Value: None	Width (Max): 0.039
Cap Unit of Meas: None	Part Weight (mg): 3.98
Tolerance: ±0.3nH	Packaged Width (lb) Arm: 0.30
Voltage: None	Packaging: 7" Reel Paper Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: 100000000
Marking: No Mark	Storage Temp Range (Packaged): -10°C to +40°C
Product Release Date: Jan. 4, 2006	Storage Temp Range (None Operating): -40°C to +125°C
Harmonization: 8504.50.40.00	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansontechnology.com/ceramic-inductors>

Printed from: <https://www.johansontechnology.com/part/LRC0603CS3N9GV001T/>