




Packaging Number

IMSA-11501S-25Y910

Category: [FFC/FPC Connectors](#)

Series: 11501

Drawings

Product 2D: [PDF ↓](#)Packaging 2D: [PDF ↓](#)Product Spec: [PDF ↓](#)

Product Details

Floating:	No
Connection Orientation:	Right Angle/Horizontal
Pitch:	0.5
Pin Count:	25
Plating:	Gold
Mount:	SMT
Boss Type:	Non
Vacuum Tape Included:	No
Terminal Material:	Corson
Part Height:	3.4

Base

Base Number:	B
Mold Material:	LCP
Packaging Type:	Tape

Environmental

Beryllium & Halogen Free:	Yes
---------------------------	-----

Advanced

Rating Voltage AC / DC:	50 volts/ 50 volts
Current Rating:	0.5A
High Speed:	No
Data Transfer Rate (Gbps):	3.0

Inquire About This Product

*Full Name**

*Email Address**

IMSA-11501S-25Y910

*Message**

Get Started

Related Technologies



Auto I-Lock

Automatic locks make single action assembly easy and reliable.

Learn More



I-Lock

IRISO's unique "I-LOCK" technology prevents accidental cable removal.

Learn More

[IRISO Home](#) > [Products](#) > [Product](#)

Products

[Find A Product](#)

[Board to Board Connectors](#)

Product Info

[Board to Board Connectors](#)

[FFC/FPC Connectors](#)

Technologies

[Floating](#)

[Two Point Contact](#)

Other

[About IRISO](#)

[News & Stories](#)

[FFC/FPC Connectors](#)

[Compression Connectors](#)

[Pin Header Connectors](#)

[Socket Connectors](#)

[Interface Connectors](#)

[ESD / Card Connectors](#)

[Input / Output Connectors](#)

[Find a Mate](#)

[Compression Connectors](#)

[Pin Header Connectors](#)

[Socket Connectors](#)

[Interface Connectors](#)

[ESD / Card Connectors](#)

[Input / Output Connectors](#)

[Z-Move](#)

[I-Lock](#)

[Auto I-Lock](#)

Industries

[Aerospace](#)

[Automotive](#)

[Consumer Electronics](#)

[Industrial Automation](#)

[Medical](#)

[Network / Telecom](#)

[Appliances](#)

[Help & FAQs](#)

[Sitemap](#)

[Contact Us](#)

Intl. Sites

[Japan](#)

[Korea](#)

[China](#)



Copyright © 2020 IRISO Electronics CO., LTD, All Rights Reserved.

