






FCIconnect.com

Copyright FCI



A = 2.54 * No. OF SPACES
B = A + 7.34
* AVAILABLE CIRCUITS : 8 & 20

PCB DRILLING DETAILS



ORDERING INFORMATION

10121492 08 YO 7 LF		LEAD FREE
SERIES NO.		PLATING
NO.OF CONTACTS		7 - GOLD FLASH SELECTIVE
D/R - 8 & 20		YO - STRAIGHT SOLDER

TECHNICAL SPECIFICATION

INSULATOR MATERIAL	: SELF EXTINGUISHING THERMOPLASTIC (UL94 V0)
CONTACT MATERIAL	: COPPER ALLOY
MAXIMUM VOLTAGE	: 1000 V rms.
NOMINAL CURRENT	: 3A AT 20°C
INSULATION RESISTANCE	: ≥ 5000 M Ω
CONTACT RESISTANCE	: ≤ 20 m Ω
CLIMATIC CATAGORY	: -55°C TO +125°C / 21 DAYS EXPOSURE TO- INDUSTRIAL ENVIRONMENT HUMIDITY TEST AS HE-14.

NOTES :

- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004

mat'l. code				surface		tolerance		projection		product family			
REF TECH SPEC				ISO 1302		ISO 406 ISO 1101		MM		8614			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A	-	GRM	2013-07-12	angles		linear				FEMALE CONNECTOR			
				0°±1°						(DUAL ROW SS WITH POL.)			
				dr	MINI K VANDANATH		2012-06-13			dwg no		sheet 1 of 1	size
				enr	ALEX BABU		2012-06-13			10121492			A3
				chr	ALEX BABU		2012-06-13						
				appd	BIJU K P		2012-06-13			type		Product Customer	Drawing
sheet index	revision	A											
	sheet	1											